



# S3127

LU70/MED  
70 watt; High Pressure Sodium HID; Medium base; ED17;  
Clear; 22 CRI; 2100K

### Features

- High Efficacy
- Long Life
- Universal operating position



S3127

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	ANSI Code	Lamp Code
S3127	045923031274	70	ED17	Medium	E26	S62	LU70/MED

Finish	MOL In Inches	MOD In Inches	Average Rated Hours	Initial Lumens	Kelvin Temp	Pack	CRI
Clear	5 7/16"	2.13"	24000	6300	2100	12	22

Burning Position	RoHS Compliant
Universal	Yes



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S3127

LU70/MED  
70 watt; High Pressure Sodium HID; Medium base; ED17;  
Clear; 22 CRI; 2100K

### Features

- High Efficacy
- Long Life
- Universal operating position



S3127

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	ANSI Code	Lamp Code
S3127	045923031274	70	ED17	Medium	E26	S62	LU70/MED

Finish	MOL In Inches	MOD In Inches	Average Rated Hours	Initial Lumens	Kelvin Temp	Pack	CRI
Clear	5 7/16"	2.13"	24000	6300	2100	12	22

Burning Position	RoHS Compliant
Universal	Yes



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

