



S3129

LU150/55/MED
150 watt; High Pressure Sodium HID; Medium base; ED17;
Clear; 22 CRI; 2100K

Features

- High Efficacy
- Long Life
- Universal operating position



S3129

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	ANSI Code	Lamp Code
S3129	045923031298	150	ED17	Medium	E26	S55	LU150/55/MED

Finish	MOL In Inches	MOD In Inches	Average Rated Hours	Initial Lumens	Kelvin Temp	Pack	CRI
Clear	5 7/16"	2.13"	24000	16000	2100	12	22

Burning Position	RoHS Compliant
Universal	Yes



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S3129

LU150/55/MED
150 watt; High Pressure Sodium HID; Medium base; ED17;
Clear; 22 CRI; 2100K

Features

- High Efficacy
- Long Life
- Universal operating position



S3129

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	ANSI Code	Lamp Code
S3129	045923031298	150	ED17	Medium	E26	S55	LU150/55/MED

Finish	MOL In Inches	MOD In Inches	Average Rated Hours	Initial Lumens	Kelvin Temp	Pack	CRI
Clear	5 7/16"	2.13"	24000	16000	2100	12	22

Burning Position	RoHS Compliant
Universal	Yes



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

