



# S3129

LU150/55/MED  
150 watt; High Pressure Sodium HID; Medium base; ED17;  
Clear; 22 CRI; 2100K

### Features

- High Efficacy
- Long Life
- Universal operating position



S3129

| Item Number | UPC          | Watts | Lamp Shape | Base   | ANSI Base | ANSI Code | Lamp Code    |
|-------------|--------------|-------|------------|--------|-----------|-----------|--------------|
| S3129       | 045923031298 | 150   | ED17       | Medium | E26       | S55       | LU150/55/MED |

| Finish | MOL In Inches | MOD In Inches | Average Rated Hours | Initial Lumens | Kelvin Temp | Pack | CRI |
|--------|---------------|---------------|---------------------|----------------|-------------|------|-----|
| Clear  | 5 7/16"       | 2.13"         | 24000               | 16000          | 2100        | 12   | 22  |

| Burning Position | RoHS Compliant |
|------------------|----------------|
| Universal        | Yes            |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S3129

LU150/55/MED  
150 watt; High Pressure Sodium HID; Medium base; ED17;  
Clear; 22 CRI; 2100K

### Features

- High Efficacy
- Long Life
- Universal operating position



S3129

| Item Number | UPC          | Watts | Lamp Shape | Base   | ANSI Base | ANSI Code | Lamp Code    |
|-------------|--------------|-------|------------|--------|-----------|-----------|--------------|
| S3129       | 045923031298 | 150   | ED17       | Medium | E26       | S55       | LU150/55/MED |

| Finish | MOL In Inches | MOD In Inches | Average Rated Hours | Initial Lumens | Kelvin Temp | Pack | CRI |
|--------|---------------|---------------|---------------------|----------------|-------------|------|-----|
| Clear  | 5 7/16"       | 2.13"         | 24000               | 16000          | 2100        | 12   | 22  |

| Burning Position | RoHS Compliant |
|------------------|----------------|
| Universal        | Yes            |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

