



# S3162

50Q/CL/MC  
 50 watt; Halogen; T4; Clear; 2000 Average rated Hours; 750 Lumens; Mini Cand base; 120 volts

### Features

- Bright, Crisp light
- UV-Filter halogen capsule
- Uniform light output



S3162

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S3162	045923031625	50	T4	Mini Cand	E11	50Q/CL/MC	120
Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Kelvin Temp	Color	Average Rated Hours
Clear	2 1/16"	0.50"	CC-2V	750	2900	Warm White	2000
Pack	Package Type		RoHS Compliant				
480/12	Box		Yes				



National Toll-Free:  
 800.43.SATCO  
 (800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
 New York, Florida, Texas,  
 Washington, California,  
 Puerto Rico

Corporate Offices:  
 110 Heartland Blvd.,  
 Brentwood, NY 11717  
 800.437.2826 631.243.2022  
 Fax 631.243.2027





# S3162

50Q/CL/MC  
 50 watt; Halogen; T4; Clear; 2000 Average rated Hours; 750 Lumens; Mini Cand base; 120 volts

### Features

- Bright, Crisp light
- UV-Filter halogen capsule
- Uniform light output



S3162

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S3162	045923031625	50	T4	Mini Cand	E11	50Q/CL/MC	120
Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Kelvin Temp	Color	Average Rated Hours
Clear	2 1/16"	0.50"	CC-2V	750	2900	Warm White	2000
Pack	Package Type		RoHS Compliant				
480/12	Box		Yes				



National Toll-Free:  
 800.43.SATCO  
 (800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
 New York, Florida, Texas,  
 Washington, California,  
 Puerto Rico

Corporate Offices:  
 110 Heartland Blvd.,  
 Brentwood, NY 11717  
 800.437.2826 631.243.2022  
 Fax 631.243.2027

