



CLOCK HANGER RECEPTACLES, RECESSED WITH SMOOTH WALL PLATE, 15A, 125V, WHITE

S3713W | [Pass & Seymour](#)

FEATURES & BENEFITS

Clock Hanger Recessed Receptacle with Smooth Wall Plate 15amp 125volt, White

- Single recessed receptacle.
- Smooth wall plate.

SPECIFICATIONS

GENERAL INFO

Color: White
Type: Clock Hanger
Special Features: Clock Hanger
Style: Decorator, Smooth

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listed: Yes
CSA Standard: C22.2 No. 42
CUL Listing No: No
cULus: No
cURus: No
Federal Spec: Yes
UL Standard: UL498
UN SPSC: 39121406
UR: No

DIMENSIONS

Depth (US): 1.878"
Height (US): 4.478"
Width (US): 2.74"

TECHNICAL INFORMATION

Amps: 15A
NEMA Configuration Number: 5-15R

Volts: 125V
Volts (AC): 125
Grade Type: Specification

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

