



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

S39915 14W Led T8 48' 40K Singl/DBL Ended 1800LM Glass

Satco

| | |
|------------------|--|
| Catalog Number | S39915 |
| Manufacturer | Satco |
| Description | 14W T8 Led - 4 FT. - 4000K - G13 Base - 50000 Hours - 1800L - Type B - BBP - 1 or 2 Ended Wiring |
| Weight per unit | 0.5800 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|--------------|--|
| average life | 50000 |
| Base | Medium Bi Pin |
| beam angle | 210 |
| lumens | 1.8k |
| Material | Glass |
| Shape | T8 |
| Warranty | 5 Year Limited - T8 LED Bulbs - Ballast Bypass |

Material, Color, and Finish

| | |
|-------------------|-------|
| color temperature | 4000 |
| Finish | Gloss |

Dimensions and Weight

| | |
|------|----|
| Size | 48 |
|------|----|

Descriptions

| | |
|------------------------|--|
| Description | 14W LED T8 48' 40K SINGL/DBL ENDED 1800LM GLASS |
| extra long description | SATCO S39915 14T8/LED/48-840/BP/SE- |
| Long Description | 14W T8 LED - 4 ft. - 4000K - G13 Base - 50000 Hours - 1800L - Type B - BBP - 1 or 2 Ended Wiring |
| Product Type | 14T8/Led/48-840/BP/Se-De |
| Special Features | Color Temperature: Cool White ; Non-Dimmable ; Warranty: 5 Year Limited - T8 LED Bulbs - Ballast Bypass ; Enclosure Rated: Yes ; Fluorescent Equivalent: 25/28/32W ; Indoor and Outdoor ; Material: Glass ; Operating Temperature: -20C (-4F) to a maximum of +45C (+113F) ; Title 20: Yes ; Location Rating: Damp |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Satco |
| GTIN | 00045923399152 |
| Manufacturers Part Number | S39915 |
| UPC | 045923399152 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS |
| Type | T8 |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight | 0.44 |
| Weight Per each | 0.58 |

Uses, Certifications, and Standards

| | |
|-----------------------|---|
| Operating Temperature | -20C (-4F) to a maximum of +45C (+113F) |
| standard | cULus |