



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S39916 14W Led T8 48' 50K Singl/DBL Ended 1800LM Glass

Satco

Catalog Number	S39916
Manufacturer	Satco
Description	14W T8 Led - 4 FT. - 5000K - G13 Base - 50000 Hours - 1800L - Type B - BBP - 1 or 2 Ended Wiring
Weight per unit	0.4400 (lbs/each)
Product Category	Lighting

Features

average life	50000
Base	Medium Bi Pin
beam angle	210
lumens	1.8k
Material	Glass
Shape	T8
Warranty	5 Year Limited - T8 LED Bulbs - Ballast Bypass

Material, Color, and Finish

color temperature	5000
Finish	Gloss

Dimensions and Weight

Size	48
------	----

Descriptions

Description	14W LED T8 48' 50K SINGL/DBL ENDED 1800LM GLASS
extra long description	SATCO S39916 14T8/LED/48-850/BP/SE-
Long Description	14W T8 LED - 4 ft. - 5000K - G13 Base - 50000 Hours - 1800L - Type B - BBP - 1 or 2 Ended Wiring
Product Type	14T8/Led/48-850/BP/Se-De
Special Features	Color Temperature: Natural Light ; Non-Dimmable ; Warranty: 5 Year Limited - T8 LED Bulbs - Ballast Bypass ; Enclosure Rated: Yes ; Fluorescent Equivalent: 25/28/32W ; Indoor and Outdoor ; Material: Glass ; Operating Temperature: -20C (-4F) to a maximum of +45C (+113F) ; Title 20: Yes ; Location Rating: Damp

Manufacturer Information

Brand	Satco
GTIN	00045923399169
Manufacturers Part Number	S39916
UPC	045923399169



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
Type	T8

Packaging

Carton	25
Weight	0.44
Weight Per each	0.44

Uses, Certifications, and Standards

Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
standard	cULus