

Eaton S42-SP

Catalog Number: S42-SP

Eaton Arrow Hart heavy-duty universal nema power plug , #10-6 AWG, 30A/50A, Commercial|range & dryer, 250V, Back wire, Black, Brass, PVC, 6-30P, 6-50P, Screw, 1.10", PVC, Retail Box

General specifications



Product Name	Catalog Number
Eaton Arrow Hart heavy-duty universal NEMA power plug	S42-SP
	UPC
	032664517846
Product Length/Depth	Product Height
1.38 in	3.37 in
Product Width	Product Weight
2.87 in	0.455 lb
Warranty	Certifications
Refer to warranty document.	UL Listed

Product specifications

Special features

Non-grounding

Device type

Plug

Color

Black

Face/body material

PVC

Wiring method

Back wire

Features

Non-grounding

Material

PVC

Allowable wire size

#10-6 AWG

Amperage Rating

30 A/50 A

Number Of Poles

Three-pole

Contact material

Brass

Type

Angled plug

Device grade

Heavy-duty industrial specification grade

NEMA configuration

6-30P, 6-50P

Style type

Power, Universal angled body

Design type

Angled straight blade

Connection type

Screw

Number of wires

Resources

Brochures

[Flush mount receptacles sell sheet](#)

Catalogs

[Arrow Hart Buyers Guide Section B](#)

Specifications and datasheets

[Eaton Specification Sheet - S42-SP](#)

3

Cord range

1.10"

Voltage rating

250V

Application

Commercial, range and dryer

Torque rating

20 lbf-inch

Packaging type

Retail Box



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia