



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## S43010CT00 3" SS304 Rigid Conduit, 10' W/Coupling

*Cablofil*

|                  |  |
|------------------|--|
| Catalog Number   | S43010CT00   |
| Manufacturer     | Cablofil   |
| Description      | Stainless Steel Rigid Conduit, Stainless Steel Material; Polished Finish; 10 Foot; 3.068 Inch Inner Diameter; 3.5 Inch Outer Diameter; UL (Canada and Us), UL/Cul 6A, Csa C22.1 Approval; NSF/Ansi 169 Applicable Standard; 7.27 Pound Per Foot Weight |
| Weight per unit  | 7.3 (lbs/each)   |
| Product Category | Galvanized Heavy Wall Conduit  |

### Features

|                     |                 |
|---------------------|-----------------|
| Applicable Standard | NSF/ANSI 169    |
| End Style           | Threaded        |
| Material            | Stainless Steel |

### Material, Color, and Finish

|        |          |
|--------|----------|
| Finish | POLISHED |
|--------|----------|

### Dimensions and Weight

|                |            |
|----------------|------------|
| Inner Diameter | 3.068 Inch |
| Length         | 10 Foot    |
| Outer Diameter | 3.5 INCH   |

### Descriptions

|                        |  |
|------------------------|--|
| Additional Information | Constructional Feature Corrosion Resistant; Includes Coupling; Heat Tolerance -150 to 1600 Deg F   |
| Commodity Description  | Galvanized Rigid Steel Conduit   |
| Description            | 3" SS304 RIGID CONDUIT, 10' W/COUPLING   |
| extra long description | STAINLESS STEEL MATERIAL; POLISHED FINISH; 10 FOOT; 3.068 INCH INNER DIAMETER; 3.5 INCH OUTER DIAMETER; UL (CANADA AND US), UL/CUL 6A, CSA C22.1 APPROVAL; NSF/ANSI 169 APPLICABLE STANDARD; 7.27 POUND PER FOOT WEIGHT; 3 INCH TRADE SIZE; THREADED END STYLE; CONSTRUCTIONAL FEATURE CORROSION RESISTANT; INCLUDES COUPLING; HEAT TOLERANCE -150 TO 1600 DEG F |
| Long Description       | STAINLESS STEEL RIGID CONDUIT, STAINLESS STEEL MATERIAL; POLISHED FINISH; 10 FOOT; 3.068 INCH INNER DIAMETER; 3.5 INCH OUTER DIAMETER; UL (CANADA AND US), UL/CUL 6A, CSA C22.1 APPROVAL; NSF/ANSI 169 APPLICABLE STANDARD; 7.27 POUND PER FOOT WEIGHT   |
| Product Type           | Stainless Steel Rigid Conduit  |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |                          |
|---------------------------|--------------------------|
| Brand                     | CALPIPE INDUSTRIES, INC. |
| GTIN                      | 00847656000080           |
| Manufacturers Part Number | S43010CT00               |
| UPC                       | 847656000080             |

## Taxonomies, Classifications, and Categories

|                      |                         |
|----------------------|-------------------------|
| Category Description | Stainless Rigid Conduit |
|----------------------|-------------------------|

## Trade Size

|            |        |
|------------|--------|
| Trade Size | 3 INCH |
|------------|--------|

## Availability

|                     |           |
|---------------------|-----------|
| Manufacturer Status | Non-Stock |
| Status              | Inactive  |

## Packaging

|                 |                     |
|-----------------|---------------------|
| Carton          | 10                  |
| Weight          | 7.27 Pound per Foot |
| Weight Per each | 7.2699              |

## Uses, Certifications, and Standards

|          |  |
|----------|--|
| Approval | UL (Canada and US), UL/CUL 6A, CSA C22.1 |
|----------|--|