



# S4610

20T4/CL/G8  
20 watt; Halogen; T4; Clear; 2000 Average rated Hours; 180 Lumens; Bi Pin G8 base; 120 volts

### Features

- Bright, Crisp light
- UV-Filter halogen capsule
- Uniform light output



S4610

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S4610	045923046100	20	T4	Bi Pin G8	G8	20T4/CL/G8	120

Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Kelvin Temp	Color	Average Rated Hours
Clear	1 13/16"	0.50"	CC-2V	180	2900	Warm White	2000

Pack	Package Type	RoHS Compliant
960/48	Box	Yes



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S4610

20T4/CL/G8  
20 watt; Halogen; T4; Clear; 2000 Average rated Hours; 180 Lumens; Bi Pin G8 base; 120 volts

### Features

- Bright, Crisp light
- UV-Filter halogen capsule
- Uniform light output



S4610

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S4610	045923046100	20	T4	Bi Pin G8	G8	20T4/CL/G8	120

Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Kelvin Temp	Color	Average Rated Hours
Clear	1 13/16"	0.50"	CC-2V	180	2900	Warm White	2000

Pack	Package Type	RoHS Compliant
960/48	Box	Yes



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

