



S4999

250R40/1
250 watt R40 Incandescent; Clear Heat; 6000 average rated hours; Medium base; 120 volts

Features

- General Service Reflector
- Household or Commercial use
- Long Life
- Brass Base



S4999

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | Lamp Code | Voltage |
|-------------|--------------|-------|------------|--------|-----------|-----------|---------|
| S4999 | 045923049996 | 250 | R40 | Medium | E26 | 250R40/1 | 120 |

| Finish | MOL In Inches | MOD In Inches | Filament | Average Rated Hours | Pack | Package Type | RoHS Compliant |
|------------|---------------|---------------|----------|---------------------|------|--------------|----------------|
| Clear Heat | 6 1/2" | 5.00" | C-9 | 6000 | 12 | Sleeve | Yes |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S4999

250R40/1
250 watt R40 Incandescent; Clear Heat; 6000 average rated hours; Medium base; 120 volts

Features

- General Service Reflector
- Household or Commercial use
- Long Life
- Brass Base



S4999

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | Lamp Code | Voltage |
|-------------|--------------|-------|------------|--------|-----------|-----------|---------|
| S4999 | 045923049996 | 250 | R40 | Medium | E26 | 250R40/1 | 120 |

| Finish | MOL In Inches | MOD In Inches | Filament | Average Rated Hours | Pack | Package Type | RoHS Compliant |
|------------|---------------|---------------|----------|---------------------|------|--------------|----------------|
| Clear Heat | 6 1/2" | 5.00" | C-9 | 6000 | 12 | Sleeve | Yes |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

