



# S5858

MP100/ED17/U/PS  
100 watt; Metal Halide HID; Medium base; ED17; Clear; 65  
CRI; 4000K

### Features

- Uniform light distribution
- Superior performance
- High Efficiency
- Pulse Start
- Open Rated



S5858

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	ANSI Code	Lamp Code
S5858	045923058585	100	ED17	Medium	E26	M90/O	MP100/ED17/U/PS
Finish	MOL In Inches	MOD In Inches	Average Rated Hours	Initial Lumens	Kelvin Temp	Color	Pulse Start
Clear	5.44"	2.13"	10000	9500	4000	Cool White	Yes
Open Rated	Pack	Package Type	CRI	Burning Position	RoHS Compliant		
Yes	12	Box	65	Universal	Yes		



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S5858

MP100/ED17/U/PS  
100 watt; Metal Halide HID; Medium base; ED17; Clear; 65  
CRI; 4000K

### Features

- Uniform light distribution
- Superior performance
- High Efficiency
- Pulse Start
- Open Rated



S5858

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	ANSI Code	Lamp Code
S5858	045923058585	100	ED17	Medium	E26	M90/O	MP100/ED17/U/PS
Finish	MOL In Inches	MOD In Inches	Average Rated Hours	Initial Lumens	Kelvin Temp	Color	Pulse Start
Clear	5.44"	2.13"	10000	9500	4000	Cool White	Yes
Open Rated	Pack	Package Type	CRI	Burning Position	RoHS Compliant		
Yes	12	Box	65	Universal	Yes		



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

