



S5878

MS400/ED28 /PS /U /4K
400 watt; Metal Halide HID; Mogul base; ED28; Clear; 65 CRI;
4200K

Features

- Uniform light distribution
- Superior performance
- High Efficiency
- Pulse Start



S5878

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	ANSI Code	Lamp Code
S5878	045923058783	400	ED28	Mogul	E39	M155/E	MS400/ED28 /PS /U /4K

Finish	MOL In Inches	MOD In Inches	Average Rated Hours	Initial Lumens	Kelvin Temp	Color	Pulse Start
Clear	8.31"	3.56"	20000	44000	4200	Cool White	Yes

Pack	Package Type	CRI	Burning Position	RoHS Compliant
12	Box	65	Universal	Yes



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S5878

MS400/ED28 /PS /U /4K
400 watt; Metal Halide HID; Mogul base; ED28; Clear; 65 CRI;
4200K

Features

- Uniform light distribution
- Superior performance
- High Efficiency
- Pulse Start



S5878

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	ANSI Code	Lamp Code
S5878	045923058783	400	ED28	Mogul	E39	M155/E	MS400/ED28 /PS /U /4K

Finish	MOL In Inches	MOD In Inches	Average Rated Hours	Initial Lumens	Kelvin Temp	Color	Pulse Start
Clear	8.31"	3.56"	20000	44000	4200	Cool White	Yes

Pack	Package Type	CRI	Burning Position	RoHS Compliant
12	Box	65	Universal	Yes



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

