



# S6237

13T2/50  
13 watt; Mini Spiral Compact Fluorescent; 5000K; 82 CRI;  
Medium base; 120 volts; 4-pack

### Features

- Self-ballasted Spiral CFL
- Uses 75% less energy than equivalent incandescent lamps
- Long Life
- Instant On
- 4-Bulb Value Pack



S6237

| Item Number  | UPC           | Watts         | Lamp Shape     | Base                | ANSI Base   | Lamp Code     | Incandescent Equivalent |
|--------------|---------------|---------------|----------------|---------------------|-------------|---------------|-------------------------|
| S6237        | 045923062377  | 13            | T2             | Medium              | E26         | 13T2/50       | 60W                     |
| Voltage      | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp | Color         | Pack                    |
| 120          | 4.13"         | 1.81"         | 880            | 12000               | 5000        | Natural Light | 12                      |
| Package Type | CRI           | ENERGY STAR   | RoHS Compliant | UL Listed           |             |               |                         |
| Box          | 82            | ENERGY STAR   | Yes            | Yes                 |             |               |                         |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S6237

13T2/50  
13 watt; Mini Spiral Compact Fluorescent; 5000K; 82 CRI;  
Medium base; 120 volts; 4-pack

### Features

- Self-ballasted Spiral CFL
- Uses 75% less energy than equivalent incandescent lamps
- Long Life
- Instant On
- 4-Bulb Value Pack



S6237

| Item Number | UPC          | Watts | Lamp Shape | Base   | ANSI Base | Lamp Code | Incandescent Equivalent |
|-------------|--------------|-------|------------|--------|-----------|-----------|-------------------------|
| S6237       | 045923062377 | 13    | T2         | Medium | E26       | 13T2/50   | 60W                     |

  

| Voltage | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp | Color         | Pack |
|---------|---------------|---------------|----------------|---------------------|-------------|---------------|------|
| 120     | 4.13"         | 1.81"         | 880            | 12000               | 5000        | Natural Light | 12   |

  

| Package Type | CRI | ENERGY STAR | RoHS Compliant | UL Listed |
|--------------|-----|-------------|----------------|-----------|
| Box          | 82  | ENERGY STAR | Yes            | Yes       |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

