



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S7949 18" 15W T8 41K Fluorescent Tube

Satco

Catalog Number	S7949
Manufacturer	Satco
Description	Fluorescent T8 Linear Lamp, Designation: F15T8/CW, 15 WTT, T8 Shape, G13 Medium Bi Pin Base, 7500 HR, Lumens: 850 LM Initial, 4100 Deg K Color Temperature, Cool White 62 Cri, 17-25/32 In Length, 1 In Diameter
Weight per unit	0.1800 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

average life	7500
Base	Medium Bi Pin
lumens	850
Shape	T8
Warranty	Avg. Rated Hour Limited
Wattage	15

Material, Color, and Finish

Color	White
color rendering index (cri)	62
color temperature	4100

Dimensions and Weight

Diameter	1.00
Length	17.78

Descriptions

Description	18" 15W T8 41K FLUORESCENT TUBE
extra long description	SATCO S7949 F15T8/COOL WHITE
Long Description	Fluorescent T8 Linear Lamp, Designation: F15T8/CW, 15 WTT, T8 Shape, G13 Medium Bi Pin Base, 7500 HR, Lumens: 850 LM Initial, 4100 DEG K Color Temperature, Cool White 62 CRI, 17-25/32 IN Length, 1 IN Diameter
Product Type	F15T8/Cool White

Manufacturer Information

Brand	Satco
GTIN	00045923079498
Manufacturers Part Number	S7949
UPC	045923079498



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	T8 Linear

Packaging

Carton	1
Weight Per each	0.18

Uses, Certifications, and Standards

Operating Temperature	Ballast Dependent
standard	RoHS Compliant