

S811+ Soft Starter with Digital Interface Module

S811+T30P3S



General Description

S811+ Soft Starter, 304A, T-frame, Premium, 600V rated, Level/Edge Sense, Three-pole, 24V power, 47-63 Hz, 1-2 conductors, #4 AWG to 500 kcmil wire, 120 Vdc, 240 Vac, Modbus RTU, NEMA 0, LCD display, -30°C to -50°C

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the product or eighteen (18) months from the date of shipment of the product, whichever occurs first.

Product Specifications

CE Marked

IEC 60947-4-2, EN 60947-4-2, UL Listed, UL Recognized, CSA file No. 3211-06, CSA Certified for Elevator Duty

Package: 12.500 x 19.000 x 14.500 in.

Package Weight: 45.000 lbs.

- Soft starter
- 304A
- Modbus RTU
- T-frame
- 47-63 Hz
- 240 Vac
- 120 Vdc
- Three-pole
- -30°C to -50°C
- 200-600V
- NEMA 0
- Three-phase motors
- #4 AWG to 500 kcmil
- Premium, 600V rated, Level/Edge Sense, Inline or Inside-the-Delta wiring configuration, pump control and extended ramp
- LCD
- Digital interface module
- NEMA Type 0
- 24V
- 1-2
- Inline (default) or inside the delta

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

© 2014 Eaton
All Rights Reserved
Printed in USA
August 2014

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

EAT•N

Powering Business Worldwide