

# Eaton S811+V72N3S

Catalog Number: S811+V72N3S

Eaton S811+ soft starter, Soft Starter, 290MM, 720 A, with OPT Inside the Delta

## General specifications



**Product Name**  
Eaton S811+ soft starter

**Catalog Number**  
S811+V72N3S

**UPC**  
78668559162

**Product Length/Depth**  
23.5 in

**Product Height**  
11.5 in

**Product Width**  
16.5 in

**Product Weight**  
108 lb

**Certifications**  
Contact Manufacturer

## defaultTaxonomyAttributeLabel

### Amperage Rating

850A

### Special features

30 second ramp or 450% current limit at 50°C, inside-the-delta connection

### Type

Standard

### Frame size

V

### Rating

257 kW at 230 V, 475 kW at 380-400 V, 500 kW at 440 V

## Resources

### Application notes

S8xL adjustment - Switching from S801+ to S811+

### Brochures

S811+/S801+ soft starters

### Catalogs

Product Datasheet - S811+V72N3S

Product Range Catalog Drives Engineering

Eaton's Volume 6—Solid-State Motor Control

### Drawings

Type S811+ Soft Starter - V-frame

### Installation instructions

Instructions for S811+ Soft Starter, S811+T..., S811+U..., and S811+V

### Multimedia

Soft starter DS7 up to 200 A

Soft Starter Product Family Overview

Soft Starter DS7 up to 32 A

### Specifications and datasheets

Eaton Specification Sheet - S811+V72N3S



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

# Eaton S811+V72N3S

Catalog Number: S811+V72N3S

Eaton S811+ soft starter, Soft Starter, 290MM, 720 A, with OPT Inside the Delta

## General specifications



**Product Name**  
Eaton S811+ soft starter

**Catalog Number**  
S811+V72N3S

**UPC**  
786685559162

**Product Length/Depth**  
23.5 in

**Product Height**  
11.5 in

**Product Width**  
16.5 in

**Product Weight**  
108 lb

**Certifications**  
Contact Manufacturer

## defaultTaxonomyAttributeLabel

### Amperage Rating

850A

### Special features

30 second ramp or 450% current limit at 50°C, inside-the-delta connection

### Type

Standard

### Frame size

V

### Rating

257 kW at 230 V, 475 kW at 380-400 V, 500 kW at 440 V

## Resources

### Application notes

S8xL adjustment - Switching from S801+ to S811+

### Brochures

S811+/S801+ soft starters

### Catalogs

Product Datasheet - S811+V72N3S

Product Range Catalog Drives Engineering

Eaton's Volume 6—Solid-State Motor Control

### Drawings

Type S811+ Soft Starter - V-frame

### Installation instructions

Instructions for S811+ Soft Starter, S811+T..., S811+U..., and S811+V

### Multimedia

Soft starter DS7 up to 200 A

Soft Starter Product Family Overview

Soft Starter DS7 up to 32 A

### Specifications and datasheets

Eaton Specification Sheet - S811+V72N3S



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia