



S8129

F21T5/835/ENV
21 watt; T5; Fluorescent; 3500K Neutral White; 85 CRI;
Miniature Bi Pin base

Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards



S8129

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S8129	045923081293	21	T5	Miniature Bi Pin	G5	F21T5/835/ENV	0.63"
MOL In Inches	Nominal Length	Initial Lumens	Mean Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
34"	36"	2100	1950	24000	3500	Neutral White	40
Package Type	CRI	RoHS Compliant					
Sleeve	85	Yes					



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S8129

F21T5/835/ENV
21 watt; T5; Fluorescent; 3500K Neutral White; 85 CRI;
Miniature Bi Pin base

Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards



S8129

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S8129	045923081293	21	T5	Miniature Bi Pin	G5	F21T5/835/ENV	0.63"
MOL In Inches	Nominal Length	Initial Lumens	Mean Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
34"	36"	2100	1950	24000	3500	Neutral White	40
Package Type	CRI	RoHS Compliant					
Sleeve	85	Yes					



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

