



S8424

F28T8/841/ES/ENV
28 watt; T8; Fluorescent; 4100K Cool White; 85 CRI; Medium Bi
Pin base



Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards

S8424

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S8424	045923084249	28	T8	Medium Bi Pin	G13	F28T8/841/ES/ENV	1.00"
MOL In Inches	Nominal Length	Initial Lumens	Mean Lumens	Average Rated Hours	IS Rated Hours	RS/PRS Rated Hours	Kelvin Temp
47.78"	48"	2725	2560	30000	24000	30000	4100
Color	Pack	CRI	RoHS Compliant	CEE Qualified			
Cool White	30	85	Yes	Yes			



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S8424

F28T8/841/ES/ENV
28 watt; T8; Fluorescent; 4100K Cool White; 85 CRI; Medium Bi Pin base



Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards

S8424

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S8424	045923084249	28	T8	Medium Bi Pin	G13	F28T8/841/ES/ENV	1.00"
MOL In Inches	Nominal Length	Initial Lumens	Mean Lumens	Average Rated Hours	IS Rated Hours	RS/PRS Rated Hours	Kelvin Temp
47.78"	48"	2725	2560	30000	24000	30000	4100
Color	Pack	CRI	RoHS Compliant	CEE Qualified			
Cool White	30	85	Yes	Yes			



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

