



S8457

FB32T8/835 /U6 /ENV
32 watt; T8; U-Bend Fluorescent; 3500K Neutral White; 82 CRI;
Medium Bi Pin base

Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards



S8457

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S8457	045923084577	32	T8	Medium Bi Pin	G13	FB32T8/835 /U6 /ENV	1.00"
Nominal Length	Leg Spacing	Initial Lumens	Mean Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
22.6"	6"	3000	2700	20000	3500	Neutral White	16
CRI				RoHS Compliant			
82				Yes			



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S8457

FB32T8/835 /U6 /ENV
32 watt; T8; U-Bend Fluorescent; 3500K Neutral White; 82 CRI;
Medium Bi Pin base

Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards



S8457

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S8457	045923084577	32	T8	Medium Bi Pin	G13	FB32T8/835 /U6 /ENV	1.00"
Nominal Length	Leg Spacing	Initial Lumens	Mean Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
22.6"	6"	3000	2700	20000	3500	Neutral White	16
CRI	RoHS Compliant						
82	Yes						



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

