



S8458

FB32T8/841 /U6 /ENV
32 watt; T8; U-Bend Fluorescent; 4100K Cool White; 82 CRI;
Medium Bi Pin base

Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards



S8458

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | Lamp Code | MOD In Inches |
|----------------|----------------|----------------|-------------|---------------------|-------------|---------------------|---------------|
| S8458 | 045923084584 | 32 | T8 | Medium Bi Pin | G13 | FB32T8/841 /U6 /ENV | 1.00" |
| Nominal Length | Leg Spacing | Initial Lumens | Mean Lumens | Average Rated Hours | Kelvin Temp | Color | Pack |
| 22.6" | 6" | 3000 | 2700 | 20000 | 4100 | Cool White | 16 |
| CRI | RoHS Compliant | | | | | | |
| 82 | Yes | | | | | | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S8458

FB32T8/841 /U6 /ENV
32 watt; T8; U-Bend Fluorescent; 4100K Cool White; 82 CRI;
Medium Bi Pin base

Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards



S8458

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | Lamp Code | MOD In Inches |
|----------------|----------------|----------------|-------------|---------------------|-------------|---------------------|---------------|
| S8458 | 045923084584 | 32 | T8 | Medium Bi Pin | G13 | FB32T8/841 /U6 /ENV | 1.00" |
| Nominal Length | Leg Spacing | Initial Lumens | Mean Lumens | Average Rated Hours | Kelvin Temp | Color | Pack |
| 22.6" | 6" | 3000 | 2700 | 20000 | 4100 | Cool White | 16 |
| CRI | RoHS Compliant | | | | | | |
| 82 | Yes | | | | | | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

