



S8517

75A/RS
75 watt A19 Incandescent; Frost; 5000 average rated hours;
590 lumens; Medium base; 130 volts; 4/Pack

Features

- General Service Incandescent
- Household or Commercial use
- Long Life
- Rough Service
- 130 volt



S8517

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S8517	045923085178	75	A19	Medium	E26	75A/RS	130

Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours	Pack	Package Type
Frost	4 1/8"	2.38"	C11/5	590	5000	120	4Pk

RoHS Compliant
Yes



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S8517

75A/RS
75 watt A19 Incandescent; Frost; 5000 average rated hours;
590 lumens; Medium base; 130 volts; 4/Pack

Features

- General Service Incandescent
- Household or Commercial use
- Long Life
- Rough Service
- 130 volt



S8517

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S8517	045923085178	75	A19	Medium	E26	75A/RS	130

Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours	Pack	Package Type
Frost	4 1/8"	2.38"	C11/5	590	5000	120	4Pk

RoHS Compliant
Yes



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

