





# S8952

4.5CTC/LED/3000K/E12/120V  
 4.5 watt; B11 LED; 3000K; Candelabra base; 120 volts

### Features

- Solid State LED lighting
- Decorative replacement lamp
- Long life
- Dimmable
- UL approved for totally enclosed fixtures

### Top 3 Recommended Dimmers

- Lutron® CL Family (96-101)
- Leviton® 6674 Universal
- Leviton® IPLO6 Universal



S8952

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape	Base
S8952	045923089527	120	4.5	40W	0.93	B11	Candelabra
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
E12	4.5CTC/LED/3000K/E12/120V	Dimmable	Clear	3 3/4"	1 3/8"	310	25000
Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	ENERGY STAR
3000	Warm White	80	290	-20°C (-4°F) to a maximum of +45°C (113°F)	12	CD/1	ENERGY STAR
RoHS Compliant		UL or ETL Listed		UL Classification		Warranty	
Yes		Yes		Damp		<a href="#">3 Year Limited</a>	



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027







# S8952

4.5CTC/LED/3000K/E12/120V  
 4.5 watt; B11 LED; 3000K; Candelabra base; 120 volts

### Features

- Solid State LED lighting
- Decorative replacement lamp
- Long life
- Dimmable
- UL approved for totally enclosed fixtures

### Top 3 Recommended Dimmers

- Lutron® CL Family (96-101)
- Leviton® 6674 Universal
- Leviton® IPLO6 Universal



S8952

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape	Base
S8952	045923089527	120	4.5	40W	0.93	B11	Candelabra
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
E12	4.5CTC/LED/3000K/E12/120V	Dimmable	Clear	3 3/4"	1 3/8"	310	25000
Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	ENERGY STAR
3000	Warm White	80	290	-20°C (-4°F) to a maximum of +45°C (113°F)	12	CD/1	ENERGY STAR
RoHS Compliant		UL or ETL Listed		UL Classification		Warranty	
Yes		Yes		Damp		<a href="#">3 Year Limited</a>	



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

