



S9105

7MR16/LED/40°/4K/12V/DIM
7 watts; MR16 LED; GU5.3 base; 40° beam spread; 4000K; 12 volts; Dimmable

Features

- Solid State LED lighting
- High Efficacy
- Long life
- UL approved for totally enclosed fixtures
- Dimmable

Compatible Dimmers

- Lutron® SELV300 ELV - Use with electronic low-voltage transformer
- Lutron® SLV600P (MLV) - Use with magnetic low-voltage transformer



S9105

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S9105	045923091056	7	MR16	GU5.3	GU5.3	7MR16/LED/40°/4K/12V/DIM	12
Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI
White	1 7/8"	2	540	25000	4000	Cool White	80
Pack	Beam Spread	RoHS Compliant	UL or ETL Listed				
12/48	40	Yes	Yes				



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

