



S9386

4.5PAR16/LED/40'/3000K/120V
4.5 watt PAR16 LED; 3000K; 40' beam spread; Medium base;
120 volts

Features

- Direct replacement for 45W
- Halogen PAR16 lamps
- Dimmable
- Damp location
- Approved for enclosed fixtures
- Long life - 25,000 hours
- High efficiency / environmentally friendly
- No UV or IR radiation
- 3 year warranty



S9386

| Item Number | UPC | Voltage | Watts | Incandescent Equivalent | Lamp Shape | Base | ANSI Base |
|-------------|--------------|---------|-------|-------------------------|------------|--------|-----------|
| S9386 | 045923093869 | 120 | 4.5 | 45W | PAR16 | Medium | E26 |

| Lamp Code | Dimmable/Non-Dimmable | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp | Color |
|-----------------------------|-----------------------|---------------|---------------|----------------|---------------------|-------------|------------|
| 4.5PAR16/LED/40'/3000K/120V | Dimmable | 2 7/8" | 2.00" | 370 | 25000 | 3000 | Warm White |

| CRI | Beam Spread Deg | Pack | Package Type | RoHS Compliant | UL or ETL Listed | Warranty |
|-----|-----------------|------|--------------|----------------|------------------|--------------------------------|
| 80 | 40 | 48 | Box | Yes | Yes | 3 Year Limited |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S9386

4.5PAR16/LED/40'/3000K/120V
4.5 watt PAR16 LED; 3000K; 40' beam spread; Medium base;
120 volts

Features

- Direct replacement for 45W
- Halogen PAR16 lamps
- Dimmable
- Damp location
- Approved for enclosed fixtures
- Long life - 25,000 hours
- High efficiency / environmentally friendly
- No UV or IR radiation
- 3 year warranty



S9386

| Item Number | UPC | Voltage | Watts | Incandescent Equivalent | Lamp Shape | Base | ANSI Base |
|-------------|--------------|---------|-------|-------------------------|------------|--------|-----------|
| S9386 | 045923093869 | 120 | 4.5 | 45W | PAR16 | Medium | E26 |

| Lamp Code | Dimmable/Non-Dimmable | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp | Color |
|-----------------------------|-----------------------|---------------|---------------|----------------|---------------------|-------------|------------|
| 4.5PAR16/LED/40'/3000K/120V | Dimmable | 2 7/8" | 2.00" | 370 | 25000 | 3000 | Warm White |

| CRI | Beam Spread Deg | Pack | Package Type | RoHS Compliant | UL or ETL Listed | Warranty |
|-----|-----------------|------|--------------|----------------|------------------|--------------------------------|
| 80 | 40 | 48 | Box | Yes | Yes | 3 Year Limited |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

