



# S9406

7PAR20/LED/40'/3000K/120V/D  
 7 watt PAR20 LED; 3000K; 40' beam spread; Medium base;  
 120 volts

### Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- IP65 - Wet location rated
- For Indoor and Outdoor use
- Dimmable

### Compatible Dimmers

- Leviton® 6674
- Leviton® IPL06
- Lutron® Nova T NYCL-250
- Lutron® SELV300
- Lutron® SLV600P

For a complete list of compatible dimmers see: [Dimmer Compatibility PDF](#)



S9406

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S9406	045923094064	120	7	50W	PAR20	Medium	E26
Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
7PAR20/LED/40'/3000K/120V/D	Dimmable	Silver	3 1/32"	2.50"	500	25000	3000
Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant	UL or ETL Listed
Warm White	80	40	24/6	Box	ENERGY STAR	Yes	Yes
Warranty							
<a href="#">3 Year Limited</a>							



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

