



S9407

7PAR20/LED/40'/3500K/120V/D
 7 watt PAR20 LED; 3500K; 40' beam spread; Medium base;
 120 volts

Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- IP65 - Wet location rated
- For Indoor and Outdoor use
- Dimmable

Compatible Dimmers

- Leviton® 6674
- Leviton® IPL06
- Lutron® Nova T NYCL-250
- Lutron® SELV300
- Lutron® SLV600P

For a complete list of compatible dimmers see: [Dimmer Compatibility PDF](#)



S9407

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S9407	045923094071	120	7	50W	PAR20	Medium	E26
Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
7PAR20/LED/40'/3500K/120V/D	Dimmable	Silver	3 1/32"	2.50"	500	25000	3500
Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant	UL or ETL Listed
Neutral White	80	40	24/6	Box	ENERGY STAR	Yes	Yes
Warranty							
3 Year Limited							



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

