



# S9443

15PAR38/LED/25'/4000K/120V/D  
 15 watt PAR38 LED; 4000K; 25' beam spread; Medium base;  
 120 volts

### Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- IP65 - Wet location rated
- For Indoor and Outdoor use
- Dimmable

### Compatible Dimmers

- Lutron® C.L Family of dimmers Gen 2.0-2.1-2.2
- Lutron® MAESTRO MACL-153
- Lutron® CASETEA PPD-6WCL-WH



S9443

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S9443	045923094439	120	15	90W	PAR38	Medium	E26

Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
15PAR38/LED/25'/4000K/120V/D	Dimmable	Silver	5 3/16"	4 3/4"	1200	25000	4000

Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant	UL or ETL Listed
Cool White	80	25	12/6	Box	ENERGY STAR	Yes	Yes

Warranty							
<a href="#">3 Year Limited</a>							



National Toll-Free:  
 800.43.SATCO  
 (800.437.2826)  
 www.satco.com

Distribution Centers:  
 New York, Florida, Texas,  
 Washington, California,  
 Puerto Rico

Corporate Offices:  
 110 Heartland Blvd.,  
 Brentwood, NY 11717  
 800.437.2826 631.243.2022  
 Fax 631.243.2027





# S9443

15PAR38/LED/25'/4000K/120V/D  
15 watt PAR38 LED; 4000K; 25' beam spread; Medium base;  
120 volts

### Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- IP65 - Wet location rated
- For Indoor and Outdoor use
- Dimmable

### Compatible Dimmers

- Lutron® C.L Family of dimmers Gen 2.0-2.1-2.2
- Lutron® MAESTRO MACL-153
- Lutron® CASETEA PPD-6WCL-WH



S9443

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S9443	045923094439	120	15	90W	PAR38	Medium	E26

Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
15PAR38/LED/25'/4000K/120V/D	Dimmable	Silver	5 3/16"	4 3/4"	1200	25000	4000

Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant	UL or ETL Listed
Cool White	80	25	12/6	Box	ENERGY STAR	Yes	Yes

Warranty							
<a href="#">3 Year Limited</a>							



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

