



S9498

6.5MR16/LED/40'/40K/12V
 6.5 watt; LED MR16 LED; 4000K; 40' beam spread; GU5.3 base; 12 volts

Features

- Silver back MR16 reflector
- Direct replacement for 50watt Halogen lamps
- Approved for enclosed fixtures
- Dimmable

Compatible Dimmers

- Lutron® SELV300 ELV - Use with electronic low-voltage transformer
- Lutron® SLV600P (MLV) - Use with magnetic low-voltage transformer



S9498

Item Number	UPC	Voltage	Watts	Lamp Shape	Base	ANSI Base	Lamp Code		
S9498	045923094989	12	6.5	MR16	GU5.3	GU5.3	6.5MR16/LED/40'/40K/12V		
Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color		
Dimmable	Silver Back	1 3/4"	2"	540	25000	4000	Cool White		
CRI	Beam Spread Deg	Pack	ENERGY STAR	RoHS Compliant	UL or ETL Listed	Warranty			
80	40	12/48	ENERGY STAR Pending	Yes	Yes	3 Year Limited			



National Toll-Free:
 800.43.SATCO
 (800.437.2826)
www.satco.com

Distribution Centers:
 New York, Florida, Texas,
 Washington, California,
 Puerto Rico

Corporate Offices:
 110 Heartland Blvd.,
 Brentwood, NY 11717
 800.437.2826 631.243.2022
 Fax 631.243.2027

