



S9570

4.5W CTC/LED/27K/120V
 4.5 watt C11 LED; Clear; Candelabra base; 2700K; 450 lumens; 120 volts

Features

- LED with a traditional incandescent look and feel
- Omni-directional light source
- Smooth dimming
- Replaces up to 40 watt lamps
- Long life - 15,000 hours
- Damp Location
- UL listed for totally enclosed fixtures

Compatible Dimmers

- Leviton 6674 Universal†
- Cooper TAL06P-C1†
- Lutron Nova TCL

† When used with incandescent dimmers, derate the dimmer's maximum load by 75%. Consult your local electrical code to ensure compliance.



S9570

| Item Number | UPC | Voltage | Watts | Incandescent Equivalent | Lamp Shape | Base | ANSI Base |
|--------------------------------|-----------------------|-----------------|--|-------------------------|----------------|---------------------|------------------|
| S9570 | 045923095702 | 120 | 4.5 | 40W | C11 | Candelabra | E12 |
| Lamp Code | Dimmable/Non-Dimmable | Finish | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp |
| 4.5W CTC/LED/27K/120V | Dimmable | Clear | 4 5/16" | 1.38" | 450 | 15000 | 2700 |
| Color | CRI | Beam Spread Deg | Operating Temperature | Pack | Package Type | RoHS Compliant | UL or ETL Listed |
| Warm White | 80 | 360 | -20°C (-4°F) to a maximum of +45°C (113°F) | 24/6 | Box | Yes | Yes |
| Warranty | | | | | | | |
| 3 Year Limited | | | | | | | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S9570

4.5W CTC/LED/27K/120V
 4.5 watt C11 LED; Clear; Candelabra base; 2700K; 450 lumens; 120 volts

Features

- LED with a traditional incandescent look and feel
- Omni-directional light source
- Smooth dimming
- Replaces up to 40 watt lamps
- Long life - 15,000 hours
- Damp Location
- UL listed for totally enclosed fixtures

Compatible Dimmers

- Leviton 6674 Universal†
- Cooper TAL06P-C1†
- Lutron Nova TCL

† When used with incandescent dimmers, derate the dimmer's maximum load by 75%. Consult your local electrical code to ensure compliance.



S9570

| Item Number | UPC | Voltage | Watts | Incandescent Equivalent | Lamp Shape | Base | ANSI Base |
|-------------|--------------|---------|-------|-------------------------|------------|------------|-----------|
| S9570 | 045923095702 | 120 | 4.5 | 40W | C11 | Candelabra | E12 |

| Lamp Code | Dimmable/Non-Dimmable | Finish | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp |
|-----------------------|-----------------------|--------|---------------|---------------|----------------|---------------------|-------------|
| 4.5W CTC/LED/27K/120V | Dimmable | Clear | 4 5/16" | 1.38" | 450 | 15000 | 2700 |

| Color | CRI | Beam Spread Deg | Operating Temperature | Pack | Package Type | RoHS Compliant | UL or ETL Listed |
|------------|-----|-----------------|--|------|--------------|----------------|------------------|
| Warm White | 80 | 360 | -20°C (-4°F) to a maximum of +45°C (113°F) | 24/6 | Box | Yes | Yes |

| Warranty | | | | | | | |
|--------------------------------|--|--|--|--|--|--|--|
| 3 Year Limited | | | | | | | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

