



# S9595

9A19/LED/5000K/120V  
9 watt; A19 LED; Frosted; 5000K Medium base; 240° beam spread; 120 volts; Non-Dimmable

### Features

- Solid State LED lighting
- A-Shaped replacement lamp
- Long life
- Non-Dimmable



S9595

| Item Number | UPC          | Voltage | Watts | Incandescent Equivalent | Lamp Shape | Base   | ANSI Base |
|-------------|--------------|---------|-------|-------------------------|------------|--------|-----------|
| S9595       | 045923095955 | 120     | 9     | 60W                     | A19        | Medium | E26       |

  

| Lamp Code           | Dimmable/Non-Dimmable | Finish  | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp |
|---------------------|-----------------------|---------|---------------|---------------|----------------|---------------------|-------------|
| 9A19/LED/5000K/120V | Non-Dimmable          | Frosted | 4 9/16"       | 2.38"         | 840            | 10000               | 5000        |

  

| Color         | CRI | Beam Spread Deg | Pack | Package Type | RoHS Compliant | UL or ETL Listed | Warranty                       |
|---------------|-----|-----------------|------|--------------|----------------|------------------|--------------------------------|
| Natural Light | 80  | 240             | 24/6 | Box          | Yes            | Yes              | <a href="#">3 Year Limited</a> |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S9595

9A19/LED/5000K/120V  
9 watt; A19 LED; Frosted; 5000K Medium base; 240° beam spread; 120 volts; Non-Dimmable

### Features

- Solid State LED lighting
- A-Shaped replacement lamp
- Long life
- Non-Dimmable



S9595

| Item Number | UPC          | Voltage | Watts | Incandescent Equivalent | Lamp Shape | Base   | ANSI Base |
|-------------|--------------|---------|-------|-------------------------|------------|--------|-----------|
| S9595       | 045923095955 | 120     | 9     | 60W                     | A19        | Medium | E26       |

  

| Lamp Code           | Dimmable/Non-Dimmable | Finish  | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp |
|---------------------|-----------------------|---------|---------------|---------------|----------------|---------------------|-------------|
| 9A19/LED/5000K/120V | Non-Dimmable          | Frosted | 4 9/16"       | 2.38"         | 840            | 10000               | 5000        |

  

| Color         | CRI | Beam Spread Deg | Pack | Package Type | RoHS Compliant | UL or ETL Listed | Warranty                       |
|---------------|-----|-----------------|------|--------------|----------------|------------------|--------------------------------|
| Natural Light | 80  | 240             | 24/6 | Box          | Yes            | Yes              | <a href="#">3 Year Limited</a> |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

