



S9639

16.5BR40/LED/3000K/1230L/120V
 16.5 watt; LED BR40; 3000K; 103' beam spread; Medium base;
 120 volts; Dimmable

Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable



S9639

| Item Number | Product Line | UPC | Voltage | Watts | Incandescent Equivalent | Power Factor | Lamp Shape |
|-------------|--------------|--------------|---------|-------|-------------------------|--------------|------------|
| S9639 | DiTTO | 045923096396 | 120 | 16.5 | 75W | 0.92 | BR40 |

| Base | ANSI Base | Lamp Code | Dimmable/Non-Dimmable | Finish | MOL In Inches | MOD In Inches | Initial Lumens |
|--------|-----------|-------------------------------|-----------------------|---------|---------------|---------------|----------------|
| Medium | E26 | 16.5BR40/LED/3000K/1230L/120V | Dimmable | Frosted | 6 7/16" | 5.00" | 1230 |

| Average Rated Hours | Kelvin Temp | Color | CRI | Beam Spread Deg | Pack | Package Type | RoHS Compliant |
|---------------------|-------------|------------|-----|-----------------|------|--------------|----------------|
| 25000 | 3000 | Warm White | 80 | 103 | 12/6 | Box | Yes |

| UL or ETL Listed | UL Classification | Warranty |
|------------------|-----------------------------|--------------------------------|
| Yes | cULus - Damp Location Rated | 3 Year Limited |



National Toll-Free:
 800.43.SATCO
 (800.437.2826)
 www.satco.com

Distribution Centers:
 New York, Florida, Texas,
 Washington, California,
 Puerto Rico

Corporate Offices:
 110 Heartland Blvd.,
 Brentwood, NY 11717
 800.437.2826 631.243.2022
 Fax 631.243.2027





S9639

16.5BR40/LED/3000K/1230L/120V
16.5 watt; LED BR40; 3000K; 103' beam spread; Medium base;
120 volts; Dimmable

Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable



S9639

| Item Number | Product Line | UPC | Voltage | Watts | Incandescent Equivalent | Power Factor | Lamp Shape |
|---------------------|-----------------------------|-------------------------------|--------------------------------|-----------------|-------------------------|---------------|----------------|
| S9639 | DiTTO | 045923096396 | 120 | 16.5 | 75W | 0.92 | BR40 |
| Base | ANSI Base | Lamp Code | Dimmable/Non-Dimmable | Finish | MOL In Inches | MOD In Inches | Initial Lumens |
| Medium | E26 | 16.5BR40/LED/3000K/1230L/120V | Dimmable | Frosted | 6 7/16" | 5.00" | 1230 |
| Average Rated Hours | Kelvin Temp | Color | CRI | Beam Spread Deg | Pack | Package Type | RoHS Compliant |
| 25000 | 3000 | Warm White | 80 | 103 | 12/6 | Box | Yes |
| UL or ETL Listed | UL Classification | | Warranty | | | | |
| Yes | cULus - Damp Location Rated | | 3 Year Limited | | | | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

