



S9723

15T8/LED/48-850/BP/120-277V
15 watt T8 LED; Medium bi-pin base; 5000K; 50000 average rated hours; 1800 lumens



Features

- No ballast or external driver required
- Direct wire 120-277V line voltage*
- All glass tube
- -20°C (-4°F) to 45°C (113°F) - ambient operating temperature
- Long life: 50,000 hours
- cULus classified - Damp location
- 5 year warranty
- DLC listed

S9723

* Install only in non-shunted lampholders

Item Number	UPC	Voltage	Watts	Fluorescent Equivalent	Lamp Shape	Base	ANSI Base
S9723	045923097232	120-277	15	25-32	T8	Medium BiPin	G13

Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
15T8/LED/48-850/BP/120-277V	Non-Dimmable	Gloss White	48"	1.00"	1800	50000	5000

Color	CRI	Beam Spread Deg	Pack	RoHS Compliant	UL or ETL Listed	UL Classification	Warranty
Natural Light	82	230	10	Yes	Yes	cULus - Damp Location Rated	5 Year Limited



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S9723

15T8/LED/48-850/BP/120-277V
15 watt T8 LED; Medium bi-pin base; 5000K; 50000 average
rated hours; 1800 lumens



Features

- No ballast or external driver required
- Direct wire 120-277V line voltage*
- All glass tube
- -20°C (-4°F) to 45°C (113°F) - ambient operating temperature
- Long life: 50,000 hours
- cULus classified - Damp location
- 5 year warranty
- DLC listed

S9723

* Install only in non-shunted lampholders

Item Number	UPC	Voltage	Watts	Fluorescent Equivalent	Lamp Shape	Base	ANSI Base
S9723	045923097232	120-277	15	25-32	T8	Medium BiPin	G13

Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
15T8/LED/48-850/BP/120-277V	Non-Dimmable	Gloss White	48"	1.00"	1800	50000	5000

Color	CRI	Beam Spread Deg	Pack	RoHS Compliant	UL or ETL Listed	UL Classification	Warranty
Natural Light	82	230	10	Yes	Yes	cULus - Damp Location Rated	5 Year Limited



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

