

# Eaton SAL06P-LA

Catalog Number: SAL06P-LA

Eaton Slide Dimmer, Maintained, 60 Hz, LED, CFL, incandescent, halogen, fluorescent, MLF, ELV , Polycarbonate, Flush, Single-pole, Single-phase



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton slide dimmer	SAL06P-LA
<b>UPC</b>	<b>Product Length/Depth</b>
032664730955	2 in
<b>Product Height</b>	<b>Product Width</b>
4.25 in	2 in
<b>Product Weight</b>	<b>Certifications</b>
0.24 lb	cULus Listed NOM

## Product specifications

### Special features

No neutral required

### Phase

Single-phase

### Load type

ELV

INC

FLR

LED

CFL

MLF

HAL

### Closure type

Maintained

### Color

Light almond

### Wiring method

Back and side

### Material

Polycarbonate

### Mounting method

Flush

### Number Of Poles

Single-pole

### Power consumption

600 W (INC, FLR, MLV, ELV)

300 W (LED and CFL)

### Frequency rating

60 Hz

### Number of ways

Three-way

### Voltage rating

120 V

### Torque rating

14 lbf-inch

## Resources

### Brochures

[Lighting controls line card brochure](#)

### Installation videos

[How to install Eaton's universal slide dimmers](#)

### Specifications and datasheets

[Eaton Specification Sheet - SAL06P-LA](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)