



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SBC6SC Split Bolt Conn Panduit Corporation

Catalog Number	SBC6SC
Manufacturer	Panduit Corporation
Description	Split Bolt Connector, #8 Awg (Stranded) Conductor Size, #6 Awg (Stranded) Conductor Size, Non-Insulated, Copper Conductor Material, 0.95 In Overall Length, 1 LB/Ea
Weight per unit	1.0 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Copper
media	Yes
Voltage Rating	600 V

Descriptions

Also Known As...	Bug Monkey balls Kearnys Split Bolt Connector
Description	SPLIT BOLT CONN
extra long description	PAN SBC6S-C Pan-Lug™ SBC6S-C Mech C
similar brands	Servit®

Manufacturer Information

Brand	PANDUIT
GTIN	00074983904037
UPC	074983904037

Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	Mechanical Split Bolt Connector

Packaging

Carton	1
Package	100
Weight Per each	1

Uses, Certifications, and Standards

standard	UL listed to 467 and 486 and CSA certified for use up to 600V & Temperature Rated to 90°C
----------	---