



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SC20 20A 600V TD Class G Fuse *Bussmann Fuses*

Catalog Number	SC20
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series Class G Fuse, SC, Fast-Acting, Current Limiting Fuse, 20 A, Rejection Style Fuse, Interrupting Rating Of 100 Ka At 600 Vac and 10 Ka At 170 VDC
Weight per unit	0.0200 (lbs/each)
Product Category	Dual Element

Features

amperage rating	20 Amp
class	G
connection	Ferrule End X Ferrule End
dimensions	1.3750 IN X 0.3750 IN X 0.3750 IN
interrupt rating	100000 Amp (RMS Symmetrical), 10000 Amp (DC)
media	Yes
Voltage Rating	600 Vac, 170 Vdc

Dimensions and Weight

Size	0.41 In Diameter X 1.41 In Length
------	-----------------------------------

Descriptions

Description	20A 600V TD CLASS G FUSE
extra long description	BUSS SC-20 BUSS SC FUSE CLASS G CLA
Features	Bussmann's SC type fuses are UL Class G and provide fast-acting (1/2-6 A) and time-delay (7-60 A) characteristics for circuit protection need. SC fuses are size rejecting in terms of their overall length thereby aiding in the prevention of overfusing
Long Description	Eaton Bussmann Series Class G fuse, SC, fast-acting, current limiting fuse, 20 A, rejection style fuse, interrupting rating of 100 kA at 600 Vac and 10 kA at 170 Vdc
Product Type	Buss SC Fuse Class G Class G
Special Features	Rejection Style

Manufacturer Information

Brand	COOPER BUSSMANN
GTIN	00051712250207
Manufacturers Part Number	SC-20
UPC	051712250207

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	FUSE



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	10
Weight Per each	0.02

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems
standard	RoHS Compliant,CE Marked