



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SC38 3/8" Flex Conn D/C Squeeze Type *Appleton/Oz Gedney*

Catalog Number	SC38
Manufacturer	Appleton/Oz Gedney
Description	Features:1.06IN Dia X 1.5IN Length, 0.48 In Thread Length, Flexible Metal Conduit, Application:Dry Location, Standard:UI 514B, Csa C22.2, Nema FB-1, Size:0.375IN, Connection:Male NPS Thread, Material:Zinc Die Cast
Weight per unit	0.0600 (lbs/each)
Product Category	Liquid Tight Fittings

Features

angle	Straight
connection	Male NPS Thread
Connector Type	Squeeze
insulation	Non Insulated
Material	Zinc Die Cast

Material, Color, and Finish

Color	Metallic
Finish	Natural

Dimensions and Weight

Size	0.375
------	-------

Descriptions

Description	3/8" FLEX CONN D/C SQUEEZE TYPE
extra long description	EGS SC-38 3/8 IN SQUEEZE CONN FLEX/
Long Description	Features:1.06IN Dia X 1.5IN Length, 0.48 IN Thread Length, Flexible Metal Conduit, Application:Dry Location, Standard:UL 514B, CSA C22.2, NEMA FB-1, Size:0.375IN, Connection:Male NPS Thread, Material:Zinc Die Cast
Product Type	3/8 In Squeeze Conn Flex/Ac
Special Features	1.06 IN Dia X 1.5 IN Length, 0.48 IN Thread Length, Flexible Metal Conduit

Manufacturer Information

Brand	Appleton
GTIN	00687855200382
Manufacturers Part Number	SC-38
UPC	687855200382

Taxonomies, Classifications, and Categories

Category Description	FLEX & MC FITTINGS
Type	Straight Squeeze Connector



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Trade Size

Trade Size 0.5

Packaging

Carton 50

Package 500

Weight Per each 0.06

Uses, Certifications, and Standards

Application Terminates flexible metal conduit to a knockout in a dry location
box or enclosure

environmental conditions Dry Location

nema rating FB-1

standard UL Standard: 514B; UL Listed: E32539, CSA Standard: C22.2 No.
18.3, CSA Certified: 208044; NEMA: FB-1