



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4030 Pleasantdale Rd Suite F
30340-0000, GA Doraville
Phone: 678-710-9550
Fax: 678-710-9551



SC4 #4 Cu Butt Splice *Nsi Industries*

Catalog Number	SC4
Manufacturer	Nsi Industries
Description	Butt Splice Connector, #6 Awg Conductor Size, #4 Awg Conductor Size, Non-Insulated, Copper Conductor Material, Gray (Code) Insulation Color, 2 Conductors, +90 °C Operating Temperature, 1 In Overall Length, Compression Terminal, 600 V, 0.03 LB/Ea
Weight per unit	0.0300 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Copper
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Gray
Finish	Tin Plated

Dimensions and Weight

Size	L=1.00 - OD=.340 - ID=.250
------	----------------------------

Descriptions

Description	#4 CU BUTT SPLICE
extra long description	NSI SC-4 4 AWG Copper Short Barrel
Features	StandardBarrel TinnedCopperSplice4 AWG Standard Barrel Tinned CopperSplices is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.

Manufacturer Information

GTIN	00662381037022
UPC	662381037022

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Short Barrel - CU Splice

Packaging

Carton	1
Package	100
Weight Per each	0.03



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4030 Pleasantdale Rd Suite F
30340-0000, GA Doraville
Phone: 678-710-9550
Fax: 678-710-9551

Uses, Certifications, and Standards

Application
standard

Terminate, Splice, Tap Power Connectors
UL486A/B, UL467 (8 AWG -3/0 AWG)