



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## SCS30X 3/0AWG Cu Butt Splice Panduit Corporation

Catalog Number	SCS30X
Manufacturer	Panduit Corporation
Description	The SCS3/0-X Copper Compression Lug Lug, Standard Barrel, Has Color-Coded Barrels Marked With Panduit and Specified Competitor Die Index Numbers For Proper Crimp Die Selection. An Inspection Window Aids to Visually Assure Full Conductor Insertion, and The Tin-Plate Material Helps to Inhibit Corrosion. UI Listed and Csa Certified to 35 KV and Temperature Rated to 90°C.
Weight per unit	0.0930 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Copper
media	Yes
Voltage Rating	NA

### Material, Color, and Finish

Color	Orange
Finish	Tin-Plated

### Dimensions and Weight

Size	NA
------	----

### Descriptions

Description	3/0AWG CU BUTT SPLICE
extra long description	PAN SCS3/0-X Pan-Lug™ SCS3/0-X Comp
Long Description	The SCS3/0-X Copper Compression Lug Lug, standard barrel, has color-coded barrels marked with Panduit and specified competitor die index numbers for proper crimp die selection. An inspection window aids to visually assure full conductor insertion, and the tin-plate material helps to inhibit corrosion. UL Listed and CSA Certified to 35 KV and temperature rated to 90°C.
Product Type	Pan-Lug™ SCS3/0-X Comp. Splice, Tin PLT Copper, PK10

### Manufacturer Information

Brand	PANDUIT
GTIN	00074983903351
Manufacturers Part Number	SCS3/0-X
UPC	074983903351



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Compression Splice

## Packaging

Carton	1
Package	40
Weight Per each	0.093

## Uses, Certifications, and Standards

Mounting standard	1 UL listed and CSA certified for use up to 600V & Temperature Rated to 90°C
----------------------	--