



SG75A	3/4	1.466	.481	1.470
SG50A	1/2	1.511	.511	1.277
SG380A	3/8	1.090	.490	1.077
SG38A	3/8	1.090	.490	1.077
PART No.	TRADE SIZE	"A"	"B"	"C"