



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **SG3A0225KB D16 SNTL-G 3PH 225KVA 480D-208Y/120V AI 60HZ 150C** *Hammond Power Solutions*

Catalog Number	SG3A0225KB
Manufacturer	Hammond Power Solutions
Description	600V Class Three Phase DOE2016 and Nrcan 2019 Compliant Energy Efficient Distribution Transformer, 480D PV, 208Y/120 SV, 225 Kva, 3PH, Aluminum Wound
Weight per unit	1,350.0 (lbs/each)
Product Category	Three Phase Energy Efficient D

### Features

kva rating	225
Number of Phases	3
Number of Taps	ST-20 compliant
Phase	A - 3PH Delta-Wye-N
Primary Voltage	480D
Secondary Voltage	208Y/120

### Dimensions and Weight

Height	52
Length	34
Width	37.5

### Descriptions

Description	D16 SNTL-G 3PH 225KVA 480D-208Y/120V AL 60HZ 150C
extra long description	HMND SG3A0225KB D16/NRC19 3PH 225kv
Features	Optional infrared windows available
Long Description	600V Class Three Phase DOE2016 and NRCan 2019 Compliant Energy Efficient Distribution Transformer, 480D PV, 208Y/120 SV, 225 kVA, 3PH, Aluminum Wound
Product Type	D16/NRC19 3PH 225KVA 480D-208Y/120V AI
Special Features	Meets current DOE 10 CFR part 431 (2016) and C802.2 efficiencies in an outdoor type enclosure. Smaller kVA sizes have standard input and/or output lugs, knockouts, and wall mounting brackets to save installation costs.

### Manufacturer Information

Brand	HPS
GTIN	00803423121976
Manufacturers Part Number	SG3A0225KB
UPC	803423121976



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	3 PHASE TRANSFORMERS
Type	Transformer > Distribution > DOE 2016 Energy Efficient > General Purpose > Three Phase

## Packaging

Carton	1
Weight Per each	1350

## Uses, Certifications, and Standards

Application	General purpose for supplying appliance, lighting, motorized machine and power loads from electrical distribution systems.
Enclosure	DH5-N3R - Indoor or Outdoor
Frequency Rating	60
Mounting standard	Floor Mount CSA, UL
Temperature Rating	Typical 30 Average/ 40 Maximum