



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SG3N0050LE D16 SNTL-G3 1PH 50KVA 240X480-120/240V AI 60HZ 150 *Hammond Power Solutions*

Catalog Number	SG3N0050LE
Manufacturer	Hammond Power Solutions
Description	600V Class Single Phase DOE2016 and Nrcan 2019 Compliant Energy Efficient Distribution Transformer, 240X480 PV, 120/240 SV, 50 Kva, 1PH, Aluminum Wound
Weight per unit	350.0 (lbs/each)
Product Category	20170801100053

Features

kva rating	50
Number of Taps	ST-20 compliant
Phase	N- 1PH Dual-Dual
Primary Voltage	240x480
Secondary Voltage	120/240

Dimensions and Weight

Height	28.75
Length	23.75
Width	25.75

Descriptions

Description	D16 SNTL-G3 1PH 50KVA 240X480-120/240V AL 60HZ 150
extra long description	HMND SG3N0050LE D16/NRC19 1PH 50kVA
Features	Optional infrared windows available
Long Description	600V Class Single Phase DOE2016 and NRCan 2019 Compliant Energy Efficient Distribution Transformer, 240x480 PV, 120/240 SV, 50 kVA, 1PH, Aluminum Wound
Product Type	D16/NRC19 1PH 50KVA 240X480 120/240val
Special Features	Meets current DOE 10 CFR part 431 (2016) and C802.2 efficiencies in an outdoor type enclosure. Smaller kVA sizes have standard input and/or output lugs, knockouts, and wall mounting brackets to save installation costs.

Manufacturer Information

Brand	HPS
GTIN	00803423140663
Manufacturers Part Number	SG3N0050LE
UPC	803423140663



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	1 PHASE TRANSFORMERS
Type	Transformer > Distribution > DOE 2016 Energy Efficient > General Purpose > Single Phase

Packaging

Carton	1
Weight Per each	350

Uses, Certifications, and Standards

Application	General purpose for supplying appliance, lighting, motorized machine and power loads from electrical distribution systems.
Enclosure	NH3-N3R - Indoor or Outdoor
Frequency Rating	60
Mounting standard	Floor or Wall mount CSA, UL
Temperature Rating	Typical 30 Average/ 40 Maximum