



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Arrow Hart Specification Grade GFCI Receptacle

**SGF15W-M**

**UPC:**032664742453

### Dimensions:

- **Height:** 4.901 IN
- **Length:** 1.68 IN
- **Width:** 3.124 IN

**Weight:**.36 LB

**Warranties:** No Data

### Specifications:

- **Type:** Mid-size
- **Amperage Rating:** 15A
- **Voltage Rating:** 125V
- **Wiring Method:** Back wire and side wire
- **Circuit Interrupter Type:** GFCI
- **Color:** White
- **Contact Material:** Brass
- **Device Type:** Receptacle
- **Face/Body Material:** PVC
- **Nema Configuration:** 5-15R
- **Receptacle Type:** Two-pole, three-wire, grounding

**Supporting documents:** No Data

### Certifications:

- cULus Listed
- NOM

**Product compliance:** No Data





Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Arrow Hart Specification Grade GFCI Receptacle

**SGF15W-M**

**UPC:**032664742453

### Dimensions:

- **Height:** 4.901 IN
- **Length:** 1.68 IN
- **Width:** 3.124 IN

**Weight:**.36 LB

**Warranties:** No Data

### Specifications:

- **Type:** Mid-size
- **Amperage Rating:** 15A
- **Voltage Rating:** 125V
- **Wiring Method:** Back wire and side wire
- **Circuit Interrupter Type:** GFCI
- **Color:** White
- **Contact Material:** Brass
- **Device Type:** Receptacle
- **Face/Body Material:** PVC
- **Nema Configuration:** 5-15R
- **Receptacle Type:** Two-pole, three-wire, grounding

**Supporting documents:** No Data

### Certifications:

- cULus Listed
- NOM

**Product compliance:** No Data

