



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## SHC1024 Cord Conn, STR ML, .50-.63", 1/2", Alum *Hubbell Wiring Devices*

Catalog Number	SHC1024
Manufacturer	Hubbell Wiring Devices
Description	Cord Connector, Brown, Machined Aluminum, SHC Model, F2 Size, 0.5 to 0.62 In Cable/Cord Size, Straight Male Connection, 1/2 In Thread Size, -30 °F Operating Temperature, +225 °F Operating Temperature, 0.1 LB/Ea
Weight per unit	0.1000 (lbs/each)
Product Category	Cable & Cord Grips

### Features

Number of Conductors	Single
pallet quantity	16000

### Material, Color, and Finish

Color Code	BROWN
------------	-------

### Descriptions

Description	CORD CONN, STR ML, .50-.63", 1/2", ALUM
extra long description	HWDC SHC1024 CORD CONN, STR ML, .50
Features	Cord Connectors - Hubbell has the broadest line and the widest choice of materials in the industry. NPT hub sizes from ¼" to 3" in straight male end, 90°, 45°, female and underground feed connectors. They are available in your choice of aluminum, plated steel, nylon and stainless steel. The zinc-plated steel cord connectors offers the strength of steel and the corrosion resistance of zinc-plating. These heavy-duty connectors hold up to most manufacturing chemicals including acid solutions, solvents and oth

### Manufacturer Information

GTIN	00783585200248
series	Standard Duty
UPC	783585200248

### Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	STRAIGHT MALE

### Packaging

Carton	1
Package	50
Weight Per each	0.1



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

environmental conditions	Suitable for use in wet locations when used with a listed nylon washer between box and fitting.
Mounting	Locknut or Tapped Opening
nema rating	12;4;4X;NEMA Type 4, 4X, 12 and 13
standard	UL Listed
Temperature Rating	Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)