



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## SKCB2 #8-#2AWG DB SPLC Kit

*Nsi Industries*

Catalog Number	SKCB2
Manufacturer	Nsi Industries
Description	Easy-Splice Copper Direct Burial Butt Splice Kit For #8 to #2 Awg. Utilizing A Mechanical Copper Butt Splice and A Heavy Wall Heat Shrink Tubing to Create A Fully Insulated Splice For Copper Conductors Only. Temperature Rating: -40 C to 90 C & 600 Volt Maximum.
Weight per unit	0.1000 (lbs/each)
Product Category	Splicing & Terminating Kits

### Features

Cable Size	8-2 AWG
Cable Type	Class A-B
insulation	Heat Shrink
Voltage Rating	600 V
Warranty	1 YEAR

### Material, Color, and Finish

Color	Black
-------	-------

### Descriptions

Description	#8-#2AWG DB SPLC KIT
extra long description	NSI SKCB-2 Easy Splice CU Butt Spli
Features	Easy-Splice Copper Direct Burial Butt Splice Kit for #8 to #2 AWG Utilizing a mechanical copper butt splice and a heavy wall heat shrink tubing to create a fully insulated splice for copper conductors only. 600 Volt Maximum.
Long Description	Easy-Splice Copper Direct Burial Butt Splice Kit for #8 to #2 AWG. Utilizing a mechanical copper butt splice and a heavy wall heat shrink tubing to create a fully insulated splice for copper conductors only. Temperature Rating: -40 C To 90 C & 600 Volt Maximum.
Product Type	Easy Splice Cu Butt Splice Kit 2
Special Features	Mechanical Copper Butt Splice And Heavy Wall Heat Shrink

### Manufacturer Information

Brand	NSi
GTIN	00662381169037
Manufacturers Part Number	SKCB-2
UPC	662381169037



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... SPLICE KITS

Type ..... Copper Butt Splice Kit

## Packaging

Carton ..... 1

Package ..... 24

Weight Per each ..... 0.1

## Uses, Certifications, and Standards

Application ..... Splicing Wire

Operating Temperature ..... -40 C To 90 C