



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SMIC0100AC 120V Ac/DC Smoke/CO Combo W/Silence - UL 217 8TH

BRK Brands/Ademco/First Alert

Catalog Number	SMIC0100AC
Manufacturer	BRK Brands/Ademco/First Alert
Description	Hardwired Combo Smoke & CO Alarm With Replaceable Battery Backup. Ac 120V Interconnectable With Silence and Latching Features. Includes Ionization Smoke Sensing Technology, Electrochemical Carbon Monoxide Sensor and A 9V Alkaline Battery.
Weight per unit	0.5700 (lbs/each)
Product Category	Builders Products

Features

dimensions	1.9 in 5.6 in 5.6 in
------------	----------------------

Material, Color, and Finish

Color	White
-------	-------

Descriptions

Description	120V AC/DC SMOKE/CO COMBO W/SILENCE - UL 217 8TH
extra long description	BRK 1046871 Smoke and CO Alarm
Features	Combo Smoke and CO Alarm
Long Description	Hardwired Combo smoke & CO Alarm with replaceable battery backup. AC 120V Interconnectable with Silence and Latching features. Includes Ionization smoke sensing technology, electrochemical carbon monoxide sensor and a 9V alkaline battery.
Product Type	Alarm Combo Ac/DC SMICO100-Ac Box
Short Description	Combo Smoke and CO Alarm
Special Features	Battery Backup,End-of-Life Warning,Hardwire Interconnectivity,Hardwire Quick Connect Plug Included,Precision Detection

Manufacturer Information

Brand	BRK
GTIN	00029054022974
Manufacturers Part Number	1046871
UPC	029054022974

Taxonomies, Classifications, and Categories

Category Description	SMOKE DETECTORS
Type	Combination Smoke & Carbon Monoxide Alarm



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	12
Weight Per each	0.57

Uses, Certifications, and Standards

Application	Precision Detection
standard	Conforms to UL 217 8th Edition Standard,Conforms to STD UL2034