



SP105/41/MOG



Description 105W 120V Spiral 4100K Mogul Base
Ordering Code 81185
UNSPSC Code 39101619

Specifications	
Voltage Rating	120
Watts	105
Base Type	Mogul Screw (E39)
MOL in/mm	11.26/286
MOD in/mm	4.02/102
Approx Initial Lumens	7000
CT deg K	4100
CRI	>80
Rated Life	10,000
Special Desc	Not for use with dimmers, electronic timers, photocells, motion/occupancy sensors, or in totally enclosed fixtures. Use in dry locations only. Use in open socket type fixtures only.
Ambient Operating Temp Range	40° C (104° F) max. Open socket type fixture.

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335



SP105/41/MOG



Description 105W 120V Spiral 4100K Mogul Base
Ordering Code 81185
UNSPSC Code 39101619

Specifications	
Voltage Rating	120
Watts	105
Base Type	Mogul Screw (E39)
MOL in/mm	11.26/286
MOD in/mm	4.02/102
Approx Initial Lumens	7000
CT deg K	4100
CRI	>80
Rated Life	10,000
Special Desc	Not for use with dimmers, electronic timers, photocells, motion/occupancy sensors, or in totally enclosed fixtures. Use in dry locations only. Use in open socket type fixtures only.
Ambient Operating Temp Range	40° C (104° F) max. Open socket type fixture.

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335