



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## SP262W Plastic Wallplate 2G 2SPLEX W/Out Line WH

*Pass & Seymour/Legrand*

|                  |  |
|------------------|--|
| Catalog Number   | SP262W   |
| Manufacturer     | Pass & Seymour/Legrand   |
| Description      | Wall Plate, 2 Gang, 5 In, 0.070 In Thickness, Thermoplastic, White, 0.08721 LB |
| Weight per unit  | 0.0882 (lbs/each)  |
| Product Category | Wall Plates & Covers   |

### Features

|                 |                       |
|-----------------|-----------------------|
| cutout          | Decorator             |
| insulation      | Bare                  |
| orientation     | Vertical              |
| Wall Plate Type | Outlet, Dimmer/Switch |

### Dimensions and Weight

|      |    |
|------|----|
| Size | 5" |
|------|----|

### Descriptions

|                        |   |
|------------------------|---|
| Description            | PLASTIC WALLPLATE 2G 2SPLEX W/OUT LINE WH |
| extra long description | P&S SP262W PLATE PLASTIC 2G 2SPLEX        |

### Manufacturer Information

|                           |                  |
|---------------------------|------------------|
| Brand                     | Pass and Seymour |
| GTIN                      | 00785007680072   |
| Manufacturers Part Number | SP262W           |
| UPC                       | 785007680072     |

### Taxonomies, Classifications, and Categories

|                      |                    |
|----------------------|--------------------|
| Category Description | Residential plates |
| Type                 | Wall Plate         |

### Packaging

|                 |        |
|-----------------|--------|
| Carton          | 1      |
| Package         | 200    |
| Weight Per each | 0.0882 |

### Uses, Certifications, and Standards

|          |                     |
|----------|---------------------|
| Mounting | WALL                |
| standard | CSA, UL, CSA, UL514 |