



<b>Description</b>	85W 120V Spiral 5000K Medium Base
<b>Ordering Code</b>	81181
<b>UNSPSC Code</b>	39101619

## Specifications

<b>Voltage Rating</b>	120
<b>Watts</b>	85
<b>Base Type</b>	Medium Screw (E26)
<b>MOL in/mm</b>	9.96/253
<b>MOD in/mm</b>	4.02/102
<b>Approx Initial Lumens</b>	5350
<b>CT deg K</b>	5000
<b>CRI</b>	>80
<b>Rated Life</b>	10,000
<b>Special Desc</b>	Not for use with dimmers, electronic timers, photocells, motion/occupancy sensors, or in totally enclosed fixtures. Use in dry locations only. Use in open socket type fixtures only.
<b>Ambient Operating Temp Range</b>	40° C (104° F) max. Open socket type fixture.

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335



<b>Description</b>	85W 120V Spiral 5000K Medium Base
<b>Ordering Code</b>	81181
<b>UNSPSC Code</b>	39101619

## Specifications

<b>Voltage Rating</b>	120
<b>Watts</b>	85
<b>Base Type</b>	Medium Screw (E26)
<b>MOL in/mm</b>	9.96/253
<b>MOD in/mm</b>	4.02/102
<b>Approx Initial Lumens</b>	5350
<b>CT deg K</b>	5000
<b>CRI</b>	>80
<b>Rated Life</b>	10,000
<b>Special Desc</b>	Not for use with dimmers, electronic timers, photocells, motion/occupancy sensors, or in totally enclosed fixtures. Use in dry locations only. Use in open socket type fixtures only.
<b>Ambient Operating Temp Range</b>	40° C (104° F) max. Open socket type fixture.

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335