



SP85/50/MED



Description 85W 120V Spiral 5000K Medium Base
Ordering Code 81181
UNSPSC Code 39101619

| Specifications | |
|-------------------------------------|---|
| Voltage Rating | 120 |
| Watts | 85 |
| Base Type | Medium Screw (E26) |
| MOL in/mm | 9.96/253 |
| MOD in/mm | 4.02/102 |
| Approx Initial Lumens | 5350 |
| CT deg K | 5000 |
| CRI | >80 |
| Rated Life | 10,000 |
| Special Desc | Not for use with dimmers, electronic timers, photocells, motion/occupancy sensors, or in totally enclosed fixtures. Use in dry locations only. Use in open socket type fixtures only. |
| Ambient Operating Temp Range | 40° C (104° F) max. Open socket type fixture. |

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335



SP85/50/MED



Description 85W 120V Spiral 5000K Medium Base
Ordering Code 81181
UNSPSC Code 39101619

| Specifications | |
|-------------------------------------|---|
| Voltage Rating | 120 |
| Watts | 85 |
| Base Type | Medium Screw (E26) |
| MOL in/mm | 9.96/253 |
| MOD in/mm | 4.02/102 |
| Approx Initial Lumens | 5350 |
| CT deg K | 5000 |
| CRI | >80 |
| Rated Life | 10,000 |
| Special Desc | Not for use with dimmers, electronic timers, photocells, motion/occupancy sensors, or in totally enclosed fixtures. Use in dry locations only. Use in open socket type fixtures only. |
| Ambient Operating Temp Range | 40° C (104° F) max. Open socket type fixture. |

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335